TECHNICAL DATASHEET: **BEST LEGENDA**





TECHNICAL INFORMATION





name	layout dimensions (mm)			quantity (pcs)		weight (kg)			max. tonnage up to 24 t	
	height	length	width	layer	pallet	pcs	pallet	incl. pallet	pcs of pallets	pcs
BEST LEGENDA I	60	140	140	40	480	2.5	1200	1230	19	9120
BEST LEGENDA II	60	210	140	30	360	3.8	1356	1386	17	6120
BEST LEGENDA I	80	140	140	40	400	3.3	1330	1360	17	6800
BEST LEGENDA II	80	210	140	30	300	5.0	1500	1530	15	4500

	approximate wall thickness	consum	ption at 12 mm joint	approx. consumption of mortar	
	mm	pcs/lm	pcs/m²	kg/m²	
DECT LECTURAL	140	6.58	92	32	
BEST LEGENDA I	60	6.58	44	9	
	210	6.58	92	48	
BEST LEGENDA II	140	4.50	63	30	
	60	4.50	30	8	
BEST LEGENDA I	140	6.58	75	28	
DEST LEGENDAT	80	6.58	44	12	
	210	6.58	75	41	
BEST LEGENDA II	140	4.50	49	26	
	80	4.50	30	10	

We are holders of the Gold Certificate for complete certification according to ISO 9001, ISO 14001, ISO 50001, ISO 45001. Our products are manufactured and inspected pursuant to European harmonized standards.

EXPLANATIONS OF PICTOGRAMS





TECHNICAL INFORMATION

production standard		ion from declared dimensions	tensile	capillary absorptivity	frost resistance ČSN 73 1322	
Stallualu	width and length	height	strength	absorptivity		
ČSN EN 771-3+A1	+3/-5 mm	+3/-5 mm	≥ 30 MPa	not more than 10 g/m²s	50 cycles	

SURFACE FINISHES AND COLOURS







CARAMEL

COLORMIX AUTUMN

 surface
 characteristics
 colour

 SHARPENED
 sharpened surface on all sides of the stone, edges irregularly bevelled
 caramel, colormix autumn, colormix sahara

GENERAL INFORMATION

Universal fittings made of plain vibrated concrete with sharpened surface, which can be used as paving stones and as elements for wall construction. The elements are strong, frost-resistant, waterproof and impregnated against contamination.

The minimum shipping quantity is 1 piece. The goods are loaded on marked pallets BEST (30 kg) or BEST large (38 kg) according to the production capacity of individual plants.

During installation, it is important to follow the correct procedure according to the instructions for use (www.best.cz).





